



PRODUCT DATA SHEET

Hyperspectral Scanning Systems




Standard
version
shown

- Standard and large-format configurations for NIR-VNIR-Extended VNIR-SWIR
- Enclosed system for UV-VIS
- Moving stage, illumination, controller, gantry
- *Standard* bundled solution incl. lab software, reflectance tile, 1TB HDPU, one day of training

PRODUCT DATA SHEET

	Standard	Large-Format	Enclosed
Use with the following imaging sensors (not included)	•NIR •VNIR •Extended VNIR •SWIR		•UV-VIS
Illumination	Quartz Tungsten Halogen (QTH)		QTH and pulsed Xenon
Moving Stage	Yes		Yes
Protective Enclosure Included	No		Yes
Max Sample Size in mm (in)	250 x 240 (9.8" x 9.5")	760 x 420 (29.9" x 16.5")	250 x 240 (9.8" x 9.5")
Max Sample Weight in kg (lb)	5kg (11 lb.)	136kg / (300 lb.) (when centered on stage)	5kg (11 lb.)
Size in mm (in)	780 x 690 x 360 (31" x 27" x 14")	1297 x 1143 x 597 (51" x 45" x 24")	941 x 914 x 661 (37" x 36" x 26")
Dual-Sensor Capable	No	Yes	No
Bundled Kit Available (includes software, reflectance tile, 1TB HDPUs, Lab software, training & support)	YES 1007A-10405	Consult Headwall	Consult Headwall



May 2017

© 2017 Headwall Photonics, Inc. Information in this document is subject to change without notice. Headwall Photonics, Inc. reserves the right to change or improve its products and specifications and to make changes in content without obligation to notify any person or organization of such changes or improvements. The Hyperspec® name (and all its derivations) is a registered Trademark of Headwall Photonics, Inc. *US and/or EU Export Restrictions may apply to this Dual Use Product.

contact information
Headwall Photonics, Inc.
580 Main Street • Bolton, Massachusetts 01740
978-353-4100
information@headwallphotonics.com