

Certificate of Analysis

IARM FeF9-18

Alloy Steel / F9 / 9Cr1Mo / UNS K90941

Certified Reference Material

Certified Values listed in wt.% with associated uncertainties

As	0.006 ± 0.001	C	0.104 ± 0.002	Ca	0.002 ± 0.001	Co	0.013 ± 0.002
Cr	8.72 ± 0.07	Cu	0.093 ± 0.003	Fe	88.9 ± 0.1	Mn	0.459 ± 0.004
Mo	0.94 ± 0.01	N	0.0323 ± 0.0009	Nb	0.078 ± 0.003	Ni	0.148 ± 0.003
O	0.0025 ± 0.0003	P	0.011 ± 0.002	S	0.0036 ± 0.0003	Sb	0.0026 ± 0.0007
Si	0.345 ± 0.008	Sn	0.0062 ± 0.0004	Ti	0.0028 ± 0.0009	V	0.214 ± 0.007
W	0.0030 ± 0.0002						

Indicative Values listed in ppm

Al (206)	B (6)	Bi (<10)	Cd (<10)	H (<1)	Mg (<10)	Pb (<50)
Se (<50)	Ta (<60)	Zn (<50)	Zr (<50)			

Description and Intended Use

This Certified Reference Material is covered under the scope of accreditation to ISO 17034 by LGC Standards - Manchester, NH. As an ISO 17034 certified reference material, appropriate use of this material will fulfill the certified reference material and traceability requirements for use in ISO 17025 certified laboratories. This CRM may come in the form of a solid disk, chips, or powder. The intended use of this CRM may include, but is not limited to, the calibration of instruments and the validation of analytical methods.

Instructions for Use

1. The test surface is on the opposite side of the labeled surface, which includes the material identification. The entire thickness of the unit is certified. However, the user is cautioned not to measure disks less than 2 mm thick when using X-ray fluorescence spectrometry. Each packaged disk has been prepared by finishing the test surface using a lathe. The user must determine the correct surface preparation procedure for each analytical technique. The user is cautioned to use care when either resurfacing the disk or performing additional polishing, as these processes may contaminate the surface.
2. The minimum sample size for chips should be individually evaluated based on the analytical technique used; this would typically be greater than 0.1 grams.
3. The material should be stored in a cool, dry location when not in use.
4. Chips are not recommended for gas analysis.

The following data represents all pertinent information reported as it applies to the chemical characterization of this material.

	As	C	Ca	Co	Cr	Cu	Fe	Mn	Mo	N	Nb	Ni	O	P	S	Sb
1	0.0032	0.1000	0.0004	0.0085	8.556	0.0845	88.600	0.4460	0.9100	0.0306	0.0710	0.1420	0.0020	0.0047	0.0027	0.0010
2	0.0055	0.1017	0.0007	0.0110	8.617	0.0880	88.787	0.4500	0.9200	0.0310	0.0730	0.1420	0.0022	0.0072	0.0028	0.0022
3	0.0058	0.1020	0.0010	0.0119	8.620	0.0896	88.840	0.4512	0.9217	0.0313	0.0730	0.1423	0.0023	0.0103	0.0032	0.0026
4	0.0060	0.1020	0.0012	0.0130	8.630	0.0900	88.900	0.4547	0.9280	0.0320	0.0744	0.1430	0.0023	0.0108	0.0036	0.0029
5	0.0070	0.1040	0.0013	0.0130	8.664	0.0900	88.900	0.4550	0.9377	0.0329	0.0762	0.1479	0.0023	0.0110	0.0036	0.0030
6	0.0070	0.1047	0.0022	0.0131	8.671	0.0925	88.953	0.4600	0.9380	0.0329	0.0770	0.1480	0.0029	0.0113	0.0037	0.0030
7	0.0071	0.1051	0.0029	0.0138	8.700	0.0930	88.967	0.4601	0.9410	0.0330	0.0798	0.1480	0.0030	0.0119	0.0039	0.0034
8	0.0082	0.1053	0.0050	0.0139	8.700	0.0938	88.970	0.4640	0.9420	0.0332	0.0800	0.1500	0.0030	0.0130	0.0040	
9		0.1070		0.0140	8.739	0.0940		0.4640	0.9570	0.0340	0.0809	0.1520		0.0136	0.0040	
10		0.1086		0.0141	8.780	0.0968		0.4657	0.9580		0.0810	0.1520		0.0140	0.0040	
11				0.0150	8.856	0.0975		0.4660	0.9581		0.0820	0.1527		0.0140	0.0040	
12				0.0190	8.908	0.1010		0.4670	0.9600		0.0857	0.1559		0.0150	0.0040	
13					8.966	0.1020		0.4670	0.9719							
14																
15																
Mean	0.0062	0.1040	0.0018	0.0134	8.724	0.0933	88.865	0.4593	0.9418	0.0323	0.0778	0.1480	0.0025	0.0114	0.0036	0.0026
STDV.	0.0015	0.0026	0.0015	0.0025	0.123	0.0051	0.125	0.0072	0.0185	0.0012	0.0044	0.0048	0.0004	0.0030	0.0005	0.0008
Certified	0.006	0.104	0.002	0.013	8.72	0.093	88.9	0.459	0.94	0.0323	0.078	0.148	0.0025	0.011	0.0036	0.0026
U_{CRM}	0.001	0.002	0.001	0.002	0.07	0.003	0.1	0.004	0.01	0.0009	0.003	0.003	0.0003	0.002	0.0003	0.0007
Methods	I,IM,I	C,O	I,IM	I,IM,O	W,I,O	I,IM,O	I	I,O	F	I,IM,O	I,IM,O	C,O	IM,I			

	Si	Sn	Ti	V	W	Al	B	Bi	Cd	H	Mg	Pb	Se	Ta	Zn	Zr
1	0.3300	0.0057	0.0008	0.1920	0.0024	0.0125	0.0002	<0.001	<0.001	0.0001	<0.001	0.0000	<0.001	0.0012	0.0006	0.0022
2	0.3320	0.0057	0.0022	0.2070	0.0029	0.0169	0.0004	<0.001	<0.001	0.0001	<0.001	0.0010	<0.005	0.0015	0.0015	0.0032
3	0.3340	0.0060	0.0022	0.2109	0.0029	0.0180	0.0005					0.0010	0.0037	0.0020	<0.001	
4	0.3370	0.0060	0.0023	0.2110	0.0030	0.0182	0.0006					0.0030	0.0060	<0.001	<0.001	
5	0.3390	0.0061	0.0025	0.2130	0.0030	0.0195	0.0011					<0.0005	<0.001	<0.001	<0.001	
6	0.3427	0.0061	0.0030	0.2154	0.0032	0.0200	<0.001					<0.001	<0.001	<0.001	<0.001	
7	0.3451	0.0063	0.0030	0.2179	0.0033	0.0210	<0.0001					<0.001	<0.001	<0.001	<0.001	
8	0.3502	0.0070	0.0040	0.2200	0.0033	0.0234	<0.001					<0.001	<0.002	<0.002	<0.005	
9	0.3510	0.0070	0.0050	0.2200		0.0260	<0.005					<0.005				
10	0.3530			0.2310		0.0300										
11																
12																
13																
14																
15																
Mean	0.3454	0.0062	0.0028	0.2138	0.0030	0.0206	0.0006			0.0001		0.0013		0.0031	0.0014	0.0027
STDV.	0.0122	0.0005	0.0012	0.0102	0.0003	0.0049	0.0003	(0.0206)	(0.0006)	(0.0001)	(0.0001)	(0.0012)	(0.0005)	0.0022	0.0007	0.0007
Certified	0.345	0.0062	0.0028	0.214	0.0030	(0.0206)	(0.0006)			(0.0001)	(0.0001)	(0.0001)	(0.0005)	(0.0006)	(0.0005)	(0.0005)
U_{CRM}	0.008	0.0004	0.0009	0.007	0.0002	IM,I	IM,I	IM,O	IM	IM	F	IM	IM,I	IM,I	IM,I	IM,I
Methods	I,O	IM,I,O	IM,I,O													

Legend: W = Classical, C = Combustion, F = Fusion, A = AA or GFAA, I = ICP or DCP, IM=ICP-MS, D = DC Arc, O = AES, X = XRF, G = GDAES or GDMS, H = Hollow Cathode AES

Certification Laboratories

Laboratory Testing, Inc.	Hatfield, PA	NSL Analytical Services	Cleveland, OH
IMR Test Labs	Lansing, NY	Dirats Laboratories	Westfield, MA
Applied Technical Services	Marietta, GA	EAG Laboratories	Liverpool, NY
LGC Standards	Manchester, NH	Luvak Laboratories Inc.	Boylston, MA
Massachusetts Materials Research Inc.	West Boylston, MA	Connecticut Metallurgical Inc	East Hartford, CT
SGS MSi	Melrose Park, IL		

Certification laboratories have demonstrated performance and traceability by utilizing a variety of test methods under the scope of ISO 17025 or have demonstrated equivalent performance. Some of the specific CRMs and SRMs used in the analysis of the material covered by this certificate are:

NIST 361 NIST 3168a NIST 184 NIST 37E

Homogeneity and Uncertainty

"Uncertainty" values, as reported adjacent to certified concentration values, are based on a 95% Confidence Interval. These estimated uncertainties include the combined effects of method imprecision, material inhomogeneity, and any bias between methods. Homogeneity data from experimental XRF results are reflected in both the overall statistics and certified data. Homogeneity samples are selected by a systematic sampling procedure. The number of samples may be determined by equation 1, where N_{prod} is the number of units produced and N_{min} is the number of samples used for homogeneity testing. These samples are arranged in a simple randomized design such that each sample is analyzed multiple times by XRF. Homogeneity may also be determined within sample using an applied version of ASTM E826. A single factor ANOVA is used to calculate uncertainty due to inhomogeneity (U_{hom}). Uncertainty of the material is calculated by equation 2, where $H=U_{hom}$, S = Standard deviation, t = t-value at 95% CI, and n = number of observations.

$$1. \quad N_{min} = \max(10, \sqrt[3]{N_{prod}})$$

$$2. \quad U_{CRM} = \frac{\sqrt{H^2 + S^2}}{\sqrt{n}} * t$$

Expiration

The certification of this material is valid indefinitely, within the uncertainty specified, provided the material is handled and stored in accordance with the instructions stated on this certificate. The certification is nullified if the material is damaged, contaminated, otherwise modified, or used in a manner for which it was not intended.

David Coler, General Manager

Analytical Reference Materials International



Analytical Reference Materials International • 276 Abby Road • Manchester, NH 03103

Telephone (603) 935-4100 • www.ARMI.com • ARMI@LGCgroup.com

IARM-FeF9-18-F

4/9/2020

2 / 2