

# Corilus - connectivity guaranteed

## Lensmeter

Essilor CL-060  
 Humphrey LA-306  
 Humphrey LA-350  
 Huvitz CLM-3100  
 Huvitz CLM-4000<sup>1</sup>  
 Luneau L-70  
 Luneau L-310  
 Luneau VL-1000  
 Luneau Wave Lens Pro  
 Nidek LM-500  
 Nidek LM-600  
 Nidek LM-600P  
 Nidek LM-770  
 Nidek LM-820  
 Nidek LM-950  
 Nidek LM-970  
 Nidek LM-990  
 Nidek LM-1000  
 Nidek LM-1000P  
 Nidek LM-1200<sup>1</sup>  
 Nidek LM-1800P  
 Shin-Nippon SLM-4000  
 Shin-Nippon SLM-5000  
 Shin-Nippon SLM-6000  
 Shin-Nippon DL-800  
 Shin-Nippon DL-900  
 Shin-Nippon DL-1000  
 Tomey TL-900  
 Tomey TL-1000  
 Tomey TL-2000C  
 Tomey TL-3000  
 Tomey TL-5000  
 Topcon CL-100  
 Topcon CL-200  
 Topcon CL-200PL

Topcon CL-300  
 Topcon CL-300PL  
 Topcon CL-1000  
 Topcon CL-2000  
 Topcon CL-2500  
 Topcon EZ-200  
 Topcon LM-P6  
 Visionix VL-3000  
 Visionix Wave Lens Pro

## Autorefractor

ARK Plusoptix  
 Canon R-22  
 Canon R-30  
 Canon R-50  
 Canon RF-10  
 HRK-9000A  
 HRK-8000A  
 Humphrey HAR-540  
 Humphrey HAR-550  
 Humphrey HAR-560  
 Humphrey HAR-580  
 Humphrey HAR-595  
 Nidek AR-310A  
 Nidek AR-600  
 Nidek AR-610  
 Nidek AR-800  
 Nidek AR-1000  
 Nidek AR-1000P  
 Nidek AR-1100  
 Righton Retinomax 2  
 Righton Retinomax 3  
 Righton Speedy-I  
 Shin-Nippon Accuref 8001  
 Shin-Nippon Accuref R-800  
 Topcon RM-8800  
 Topcon RM-A2000

Topcon RM-A3000B  
 Topcon RM-A6000  
 Topcon RM-A7000  
 Topcon RM-A8000  
 Topcon RM-A8000B

## Autorefractor Keratometer

Canon R-22  
 Canon R-50  
 Canon RK-2  
 Canon RK-5  
 Canon RK-F1<sup>1</sup>  
 Canon RK-F2<sup>1</sup>  
 Grand Seiko GR-3100K  
 Grand Seiko WR-5100K  
 Humphrey HARK-599  
 Humphrey HARK-5xx  
 Huvitz HRK-7000  
 Huvitz MRK-3100<sup>1</sup>  
 Luneau L-60  
 Luneau L-62  
 Luneau L-64  
 Luneau L-67  
 Nidek AI-Scan<sup>1</sup>  
 Nidek ARK-1A<sup>1</sup>  
 Nidek ARK-1s<sup>1</sup>  
 Nidek ARK-310A  
 Nidek ARK-510A  
 Nidek ARK-530A  
 Nidek ARK-700  
 Nidek ARK-710  
 Nidek ARK-900  
 Nidek ARK-2000  
 Nidek ARK-9000  
 Nidek OPD-Scan  
 Nidek OPD-Scan III  
 Nidek HandyRef-K

<sup>1</sup> Only SQL version

<sup>2</sup> In not SQL version, only one direction from Phoropter to PC

<sup>3</sup> All perimeters are connected to the Peridata software

<sup>4</sup> Oculus Perimetry software needed

<sup>5</sup> Zeiss Option A needed

<sup>6</sup> Capturing board needed

<sup>7</sup> Haag-Streit Eyesuite software version i4.000 needed

<sup>8</sup> Windows 7 Professional as Operating System needed

<sup>9</sup> Canon CF-1 Retinal Imaging version 3.1.1.2. needed

<sup>10</sup> Icare LINK software version 1.55 needed

<sup>11</sup> Please contact us for more information



Precision by Tradition



With special thanks to our partners



**CORILUS**  
 Connecting Care

Knokkeweg 23 / 1A  
 B - 9880 Aalter  
 info.medical@corilus.be  
 www.corilus.be  
 Tel. +32 (0) 9 325 93 93  
 Fax +32 (0) 9 325 93 95



### Autorefractor Keratometer (cont.)

Retinomax Screen  
 Righton NRK-8000  
 Righton Retinomax K-Plus  
 Righton Retinomax K-Plus 2  
 Righton Retinomax K-Plus 3  
 Righton Speedy-K  
 Righton Speedy-K2  
 Shin-Nippon Accuref K-900  
 Shin-Nippon Accuref-K 9001  
 Shin-Nippon Accuref-K 9003D  
 Shin-Nippon SPM 700  
 Tomey ARK  
 Tomey RC-5000<sup>1</sup>  
 Topcon KR-1<sup>1</sup>  
 Topcon KR-800<sup>1</sup>  
 Topcon KR-3000  
 Topcon KR-3500  
 Topcon KR-7000  
 Topcon KR-7000P  
 Topcon KR-7500P  
 Topcon KR-8100  
 Topcon KR-8100P  
 Topcon KR-8800<sup>1</sup>  
 Topcon KR-8900  
 Visuref 100<sup>1</sup>

### Autorefractor Keratometer Tonometer

Nidek RKT-7700  
 Nidek Tonoref II  
 Nidek Tonoref III  
 Topcon TRK-1P  
 Topcon TRK-2P

**Phoropter**  
 Luneau Vision Pro<sup>1</sup>  
 Möller Visutron+  
 Möller Visutron 900+  
 Nidek RT-1200  
 Nidek RT-1200S  
 Nidek RT-2100  
 Nidek RT-3100<sup>2</sup>  
 Nidek RT-5100<sup>2</sup>  
 Nikon Optotester  
 Rodenstock Phoromat 200 software  
 Rodenstock Phoromat 500 software  
 Shin-Nippon DR-900<sup>1</sup>  
 Topcon CV-2000  
 Topcon CV-2500  
 Topcon CV-3000  
 Topcon CV-5000<sup>2</sup>  
 Topcon CV-WIN

### Perimeter<sup>3</sup>

Haag-Streit Octopus 101  
 Haag-Streit Octopus 123  
 Haag-Streit Octopus 301  
 Haag-Streit Octopus 311  
 Haag-Streit Octopus 500  
 Haag-Streit Octopus 900<sup>7</sup>  
 Humphrey HFA 6xx  
 Humphrey HFA7xx  
 Oculus Centerfield<sup>4</sup>  
 Oculus Twinfield<sup>4</sup>  
 OPTOPOL PTS 920  
 OPTOPOL PTS 925  
 OPTOPOL PTS 2000  
 M700

### Biometer

Nidek AI-Scan<sup>1</sup>  
 Haag-Streit Lenstar LS 900<sup>7</sup>  
 Zeiss IOL-Master (Windows 98 model)<sup>5</sup>  
 Zeiss IOL-Master (Windows XP model)

### Bio-Pachy meter

Tomey AL-4000<sup>11</sup>

### Tonometer

Canon TX-10  
 Canon TX-20P<sup>1</sup>  
 Huvitz HNT-7000<sup>1</sup>  
 Kowa KT-800<sup>1</sup>  
 Nidek NT-510  
 Nidek NT-530P<sup>1</sup>  
 Nidek NT-1000  
 Nidek NT-2000  
 Nidek NT-2000 MIII  
 Nidek NT-3000  
 Reichert AT55  
 Reichert AT555  
 Reichert G3  
 Reichert Xpert  
 Shin-Nippon NCT-200<sup>1</sup>  
 Topcon CT-1P  
 Topcon CT 20  
 Topcon CT 40  
 Topcon CT 60  
 Topcon CT 80  
 Topcon CT 800

With special thanks to our partners



Knokkeweg 23 / 1A  
 B - 9880 Aalter  
 info.medical@corilus.be  
 www.corilus.be  
 Tel. +32 (0) 9 325 93 93  
 Fax +32 (0) 9 325 93 95



<sup>1</sup> Only SQL version

<sup>2</sup> In not SQL version, only one direction from Phoropter to PC

<sup>3</sup> All perimeters are connected to the Peridata software

<sup>4</sup> Oculus Perimetry software needed

<sup>5</sup> Zeiss Option A needed

<sup>6</sup> Capturing board needed

<sup>7</sup> Haag-Streit Eyesuite software version i4.000 needed

<sup>8</sup> Windows 7 Professional as Operating System needed

<sup>9</sup> Canon CF-1 Retinal Imaging version 3.1.1.2. needed

<sup>10</sup> Icare LINK software version 1.55 needed

<sup>11</sup> Please contact us for more information

### Image Systems Capturing<sup>6</sup>

Alcon B Scan  
Alcon Ocusan  
Haag-Streit Slitlamps CN 900<sup>7</sup>  
Haag-Streit Slitlamp IM 900<sup>7</sup>  
Konan Specular Microscope  
Righton Coolpix Slitlamp (software)  
Quantel Medical A Scan  
Quantel Medical B Scan  
Topcon Specular Microscope SP-2000

### Image Systems network interfacing<sup>1,8</sup>

Alcon Eyecubed  
Canon CF-1 Digital Retinal Camera<sup>9</sup>  
Canon Fundus Camera  
Ellex Eyecube  
Heidelberg HRT-2  
Heidelberg HRT-3  
Heidelberg HRA  
Heidelberg Spectralis  
Heidelberg OCT  
Icare PRO<sup>10</sup>  
Iconan Robo Specular  
Kowa Fundus Camera  
Nidek AFC-210 Fundus Camera  
Nidek OPD-Scan III<sup>1</sup>  
Oculus Keratograph  
Oculus Pentacam  
Optopol REVO  
Optopol REVO NX  
Opko Spectral OCT SLO  
Optovue RTVue-100 OCT  
Rhine-Tec Specular Microscope  
Tomey EM-3000 Specular Microscope  
Topcon 3D OCT Maestra<sup>12</sup>  
Topcon Image Net  
Topcon IMAGELink  
Topcon NW-100  
Topcon SP-3000P Specular Microscope  
Topcon TRC-50EX/TRC-50IX funduscamera  
Zeiss OCT  
Zeiss Visucam 200/500

### Statistics

DataGraph

### Hospital Integration

HL-7 ADT  
IHE PAM 2.5  
HL-7 ADT.QRY  
HL-7 ORU  
HL-7 SIU  
H'PRIM Santé  
H'PRIM XML  
XML

### Software context-links

Haag-Streit Eyesuite Biometry  
Haag-Streit Eyesuite Perimetry  
Haag-Streit Eyesuite Slitlamp  
Nidek Navis-Ex/Lite  
Oculus Pentacon  
Peridata  
Zeiss Forum



With special thanks to our partners



<sup>1</sup> Only SQL version

<sup>2</sup> In not SQL version, only one direction from Phorofter to PC

<sup>3</sup> All perimeters are connected to the Peridata software

<sup>4</sup> Oculus Perimetry software needed

<sup>5</sup> Zeiss Option A needed

<sup>6</sup> Capturing board needed

<sup>7</sup> Haag-Streit Eyesuite software version i4.000 needed

<sup>8</sup> Windows 7 Professional as Operating System needed

<sup>9</sup> Canon CF-1 Retinal Imaging version 3.1.1.2. needed

<sup>10</sup> Icare LINK software version 1.55 needed

<sup>11</sup> Please contact us for more information

<sup>12</sup> TopConnect software needed

Knokkeweg 23 / 1A  
B - 9880 Aalter  
info.medical@corilus.be  
www.corilus.be  
Tel. +32 (0) 9 325 93 93  
Fax +32 (0) 9 325 93 95



**CORILUS**  
Connecting Care