


[Schematic drawings]

DS ZG- DU DC -1431 Rev 1

Metenova Mixer

ZG1 & ZG2

Drive Unit DC



Option 4:
Transport Locking Device



Part #	Description	
ZG00502-01431	ZG2 Drive Unit DC, TC [ZG1 & ZG2]	
ZG00016-01773	ZG- Transport Locking Device TC [ZG1 & ZG2]	Option 4

A mm (in)	ØC mm (in)	F mm (in)	Weight kg (lb)
200 (7.87)	58 (2.28)	250 (9.84)	3.0 (6.6)

Motor:	66 W (3000 rpm - 6:1 Gear Box)
Voltage:	24 VDC
Current:	4.1A
Certified:	TÜV
Protection class:	IP 54
Environment temp:	0°C - 40°C (32°F - 104°F)
Min - Max rpm:	0 - 500
Color:	In compliance with FDA



- Soft start must be used when operating the mixer.
- Items are individually packed and for traceability purposes marked with item & id no.
- Metenova Quality Assurance System ensures the quality and traceability at all stages of the process.

Option 4: Transport Locking Device	Secures the Mix Head in place when transporting the tank without Drive Unit attached.
------------------------------------	---

Metenova AB.
Norra Ägatan 32
431 35 Mölndal Sweden
Phone +46 31 3359500

www.metenova.com
info@metenova.com

Metenova America Inc.
P.O. Box 398
Glen Gardner, NJ 08826, USA
Phone 908-537-4199

The information in this publication is subject to change without prior notice. The information in this document is believed to be complete and accurate at the time of publication. Metenova assumes no responsibility for any errors that may appear in this document. Customer is responsible for determining Metenova's product will perform suitable in the intended application.